

# Rod clevis SGA-M16X1,5

Part number: 10768

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                    |
|--------------------------------|--------------------------|
| Size                           | M16x1.5                  |
| Radial deviation +/-           | 5 mm                     |
| Angle compensation +/-         | 120 deg                  |
| Mounting position              | optional                 |
| Threaded connection            | Male thread M16x1.5      |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity         | VDMA24364-B2-L           |
| Ambient temperature            | -40 °C ... 150 °C        |
| Max. load capacity             | 4 kN                     |
| Product weight                 | 512 g                    |
| Note on materials              | RoHS-compliant           |
| Material bolt                  | Galvanised steel         |
| Material rod eye               | Steel<br>Galvanised      |
| Material lock                  | Spring steel, galvanised |