

Shock absorber DYEF-S-M5-Y1

Part number: 1152507

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------------------|---|
| Size | M5 |
| Stroke | 1.5 mm |
| Cushioning | Elastic cushioning rings/pads at both ends without metal fixed stop |
| Mounting position | optional |
| Position detection | Without |
| Max. impact speed | 0.8 m/s |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Cushioning length | 1.5 mm |
| Max. energy consumption per stroke | 0.05 J |
| Product weight | 2 g |
| Type of mounting | Via lock nut |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material housing | High-alloy steel |