

Pressure gauge PAGL-HP3-63-60-G14

Part number: 1166938

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Indicating range	0 bar ... 60 bar
Indicating range	0 MPa ... 6 MPa
Indicating range	0 psi ... 870 psi
Symbol	00991463
Conforms to standard	EN 837-1
Nominal size of pressure gauge	63
Explosion protection	The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Design	Bourdon tube pressure gauge
Type of mounting	In-line installation
Operating medium	Inert gas Neutral fluids
Note on operating and pilot medium	No acetylene No oxygen
Operating pressure	0 MPa ... 6 MPa
Operating pressure	0 bar ... 60 bar
Operating pressure	0 psi ... 870 psi
Alternating load factor	0.66
Measurement accuracy class	1.6
Degree of protection	IP65
Storage temperature	-40 °C ... 70 °C
Media temperature	0 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
Note on materials	RoHS-compliant
Position of connection	Centred, rear side
Pneumatic connection	G1/4
Material in contact with the medium	Brass
Material screwed plug	Brass
Material housing	Steel
Material screen	PS

Feature	Value
Housing colour	Silver
Product weight	80 g
Scale	Triple scale MPa (outer scale) Bar (outside scale) psi (inner scale)