


Gripper jaw blank BUB-HGPD-20

Part number: 1180948

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	20
Mounting position	optional
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	5 °C ... 60 °C
Product weight per gripper jaw	57 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS-compliant
Material unmachined part	Wrought aluminium alloy