

# Gripper jaw blank BUB-HGPD-40

Part number: 1180951

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40
Mounting position	optional
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	5 °C ... 60 °C
Product weight per gripper jaw	445 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS-compliant
Material unmachined part	Wrought aluminium alloy