


Sub-base VABS-C8-12XB-QX-D

Part number: 1236029

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Construction width	24 mm
Max. number of valve positions	1
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Max. tightening torque for valve mounting	0.48 Nm ... 0.72 Nm
Max. tightening torque wall mounting	1.3 Nm
Product weight	30 g
Pilot air port 12/14	Prepared for cartridge
Pneumatic connection, port 1	Prepared for cartridge
Pneumatic connection, port 3	Prepared for cartridge
Pneumatic connection, port 5	Prepared for cartridge
Note on materials	RoHS-compliant
Material manifold rail	PA reinforced