

Indicator insert MFLZ-24DC/AC

Part number: 12610

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Product weight	14 g
Electrical connection	Type B To industry standard (11 mm)
Nominal operating voltage DC	24 V
Nominal operating voltage AC	24 V
Mains frequency	0 Hz ... 60 Hz
Permissible voltage fluctuations	+/- 15%
Degree of protection	IP65 To IEC 60529
Ambient temperature	-20 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA6 reinforced