

Bellow gripper DHEB-14-E-U-E-P

Part number: 1320834

FESTO



 General operating condition

Data sheet

Feature	Value
Size	14
Stroke of bellows	7 mm
Min. \varnothing to be gripped	15 mm
Max. \varnothing to be gripped	19.5 mm
Mounting position	optional
Mode of operation	Single-acting Closed
Gripper function	Adaptive
Design	Contracting diaphragm Force pilot operated motion sequence
Guide	Basic guide
Position detection	Without
Operating pressure	5 bar ... 8 bar
Reset pressure	<1 bar
Max. operating frequency of gripper	≤ 4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	20 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	40 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	5 °C ... 60 °C
Average replacement interval for the bellows	0.5 MioCyc
Guide value for effective load	0.15 kg
Product weight	20 g
Type of mounting	Via male thread Via lock nut
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material bellows	EPDM
Material housing	Aluminium Anodised