

Pressure gauge MA-15-145-M5-PSI

Part number: 132341

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Indicating range	0 psi ... 145 psi
Symbol	00991463
Nominal size of pressure gauge	15
Design	Bourdon tube pressure gauge without measuring mechanism
Type of mounting	In-line installation
Operating medium	Inert gases Neutral fluids
Note on operating and pilot medium	No acetylene No oxygen
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Operating pressure	0 psi ... 145 psi
Alternating load factor	0.66
Measurement accuracy class	5
Degree of protection	IP53
Media temperature	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Position of connection	Centred, rear side
Pneumatic connection	M5
Material screwed plug	Brass
Material housing	Steel
Material screen	PC
Housing colour	Black
Product weight	10 g
Scale	Single scale psi (outer scale)