

Module connector PAML-MK-90-HP3

Part number: 1367005

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	90
Nominal size DN	36
Series	L
Operating pressure	0 MPa ... 5 MPa
Operating pressure	0 bar ... 50 bar
Operating medium	Compressed air to ISO 8573-1:2010 [:-:-]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C ... 60 °C
Media temperature	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Product weight	150 g
Note on materials	RoHS-compliant
Material seals	NBR
Material module connector	Wrought aluminium alloy
Material screws	Stainless steel