

Multi-tube connector KM-22-B

Part number: 13694

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	4 mm
Size of pack	1
Operating pressure	-0.095 MPa ... 0.8 MPa
Operating pressure	-0.95 bar ... 8 bar
Operating pressure	-13.775 psi ... 116 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B2-L
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Max. number of connections	22
Pneumatic connection	For tubing outside diameter of 3 mm For tubing O.D. 4 mm For tubing O.D. 6 mm
Note on materials	RoHS compliant