

Barbed fitting CRCN-1/4-PK-4

Part number: 13972

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal size | 3.2 mm |
| Type of seal on screwed plug | Sealing ring |
| Size of pack | 1 |
| Operating pressure complete temperature range | -0.95 bar ... 10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitable for use with food | See supplementary material information |
| Ambient temperature | 0 °C ... 60 °C |
| Product weight | 17.73 g |
| Pneumatic connection, port 1 | Male thread G1/4 |
| Pneumatic connection, port 2 | For tubing outside diameter of 6 mm |
| Note on materials | RoHS-compliant |
| Material housing | High-alloy stainless steel |
| Material thread seal | PA-reinforced TPE-U(PU) |