

Manifold sub-base NAV-1/2-NPT-3C

Part number: 13999

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	190 mm
Operating pressure	16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Mounting method for sub-base	With through-hole
Pilot air port 12	NPT1/8-27
Pilot air port 14	NPT1/8-27
Pneumatic connection, port 2	NPT1/2-14
Pneumatic connection, port 4	NPT1/2-14