

# Bellows kit EADB-V2-63-S101-200

Part number: 1488362

FESTO



 General operating condition

## Data sheet

Feature	Value
Outside diameter	93 mm
Size	63
Stroke range	101 mm ... 200 mm
Piston rod extension	68 mm
Design	Round
Mounting position	optional
Design	With ducted exhaust air
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Dust Chips Oils Grease Petrol
Degree of protection	IP65 To IEC 60529
Ambient temperature	-10 °C ... 80 °C
Moving mass	142 g
Product weight	265 g
Type of mounting	Push-on Via threaded pin
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material adapter components	Wrought aluminium alloy Anodised
Material seals	NBR
Material bellows	NBR
Material threaded pin	High-alloy stainless steel