

Programming cable NEBC-U1G4-K-1.8-N-U2G4

Part number: 1501332

FESTO



 General operating condition

Data sheet

Feature	Value
Cable designation	Without inscription label holder
Mounting position	optional
Electrical connection 1	Straight plug connector, USB 2.0 type A, 4-pin
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Plugs
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	USB 2.0 Type B
Electrical connection 1, number of connections/cores	4
Electrical connection 1, used connections/cores	4
Electrical connection 1, connection pattern	00995727
Electrical connection 2	Straight plug connector, USB 2.0 type B, 4-pin
Electrical connection 2, function	Controller side
Electrical connection 2, design	Angular
Electrical connection 2, connection type	Plugs
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connector system	USB 2.0 type A
Electrical connection 2, number of connections/cores	4
Electrical connection 2, used connections/cores	4
Electrical connection 2, connection pattern	00995726
Cable length	1.8 m
Cable characteristic	Standard
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress