

# Moment compensator FKG-40-B

Part number: 15235

FESTO



 [General operating condition](#)

## Data sheet

| Feature  | Value  |
|--|--|
| Size   | 40   |
| Radial deviation +/-                                   | 1 mm   |
| Corrosion resistance class CRC                         | 2 - Moderate corrosion stress                        |
| LABS (PWIS) conformity                                 | VDMA24364-B2-L                                       |
| Ambient temperature                                    | -20 °C ... 120 °C                                    |
| Max. permissible long-term load in force direction +/- | 1600 N   |
| Product weight   | 1227 g   |
| Material driver  | Anodised wrought aluminium alloy<br>Galvanised steel |
| Material clevis  | Steel<br>Galvanised                                  |
| Material slip piece                                    | Brass  |