

Multi-socket KDVF6-12

Part number: 152510

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	6 mm
Operating pressure	-0.95 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Max. number of connections	12
Pneumatic connection	PK-6
Colour	Grey
Note on materials	RoHS-compliant