

Manifold sub-base with angled connections NAVW-1/2-3-ISO

FESTO

Part number: 152791



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	optional
Conforms to standard	ISO 5599-1
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Ester oil < 0.1mg/m ³ , according to ISO 8573-1:2010 [-:-:2]
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C ... 80 °C
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	1020 g
Mounting method for sub-base	With through-hole
Type of mounting	With through-hole
Pilot air port 12/14	G1/8
Auxiliary pilot air port 12	G1/8
Auxiliary pilot air port 14	G1/8
Pilot air port 12	G1/8
Pilot air port 14	G1/8
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Pneumatic connection, port 4	G1/2
Material sub-base	Die-cast aluminium