

# Predetermining counter PZV-E-C

Part number: 15608

FESTO



 General operating condition

## Data sheet

Feature	Value
Design	Mechanical sequence counter with pneumatic drive
Type of reset	Pushbutton or pneumatic signal
Display	5-digit
Drop-off pressure drive	0.2 ± 0.1 bar
Drop-off pressure reset	0.15 ± 0.1 bar
Response pressure drive	0.6 ± 0.2 bar
Operating pressure	2 bar ... 8 bar
Min. reset pressure	2 bar
Min. pulse length drive	10 ms
Min. pulse length reset	180 ms
Min. pause period drive	15 ms
Min. pause period reset	50 ms
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Product weight	150 g
Type of mounting	Front panel mounting
Pneumatic connection	M5