

Barbed hose fitting N-1/2-P-13-MS

Part number: 15636

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal size	11 mm
Type of seal on screwed plug	Sealing ring
Mounting position	optional
Design	Straight design
Size of pack	1
Operating pressure complete temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	18 Nm
Product weight	47.75 g
Pneumatic connection, port 1	Male thread G1/2
Pneumatic connection, port 2	For tubing inside diameter of 13 mm
Note on materials	RoHS-compliant
Material housing	Brass