

Swivel flange SUA-12/16

Part number: 157319

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	12/16
Mounting position	optional
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 90 °C
Product weight	22 g
Note on materials	RoHS-compliant
Material mounting	Wrought aluminium alloy
Material bolt	Galvanised steel
Material sleeve	Spring steel
Material bearing	Polymer
Material screws	Galvanised steel
Material lock	Spring steel
Material shaft	Steel With protective coating