

Swivel flange SNGB-250

Part number: 157512

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	250
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 90 °C
Product weight	16141 g
Note on materials	RoHS-compliant
Material mounting	Spheroidal graphite cast iron
Material bolt	Steel Galvanised
Material bearing	Polymer
Material disc	Galvanised steel
Material screws	Steel Galvanised
Material lock	Spring steel, galvanised