

# Sensor bracket DASI-Q11-20-A-SR

Part number: 1581420

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value  |
|--------------------------------|--|
| Size                           | 20   |
| Design                         | For T-slot   |
| For piston diameter            | Ø20  |
| Design                         | Sensor rail  |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress                                    |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L  |
| Ambient temperature            | -10 °C ... 60 °C   |
| Product weight                 | 32 g   |
| Type of mounting               | Clamped in T-slot<br>Via through-hole and screw<br>Via slot nuts |
| Note on materials              | RoHS-compliant   |
| Material screws                | Steel<br>Galvanised  |