

Condensate drain WA-1-B

Part number: 158497

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of actuation	Mechanical
Mounting position	Vertical +/-10°
Manual override	Non-detenting
Condensate drain	Fully automatic
Design	External, mechanical, fully automatic
Measured variable	Fill level
Valve function	2/2-way, single solenoid, closed
Operating pressure	4 bar ... 16 bar
Operating medium	Water
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C ... 60 °C
Media temperature	0 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
Product weight	210 g
Type of mounting	Inline installation
Condensate drain connection	G1/4
Pneumatic connection	M9
Material housing	Brass Process automation