

# Flanged pressure gauge FMA-63-2,5-1/4-EN

Part number: 159601

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Indicating range	0 bar ... 2.5 bar
Indicating range	0 psi ... 36.25 psi
Symbol	00991463
Conforms to standard	EN 837-1
Nominal size of pressure gauge	63
Explosion protection	The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Design	Bourdon tube pressure gauge
Type of mounting	Front panel mounting
Operating medium	Inert gas Neutral fluids
Note on operating and pilot medium	No acetylene No oxygen
Operating pressure	0 MPa ... 0.25 MPa
Operating pressure	0 bar ... 2.5 bar
Operating pressure	0 psi ... 36.25 psi
Alternating load factor	0.66
Measurement accuracy class	2.5
Degree of protection	IP43
Media temperature	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Position of connection	Centred, rear side
Pneumatic connection	G1/4
Material in contact with the medium	Brass
Material screwed plug	Brass
Material housing	ABS
Material screen	SAN
Material mounting ring	Steel

<b>Feature</b>	<b>Value</b>
Housing colour	Black
Product weight	120 g
Scale	Double scale Bar (outside scale) psi (inner scale)