

Angled plug socket MPPE-3-B

Part number: 161839

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Frequency of connection	500
Type of mounting	Via union nut
Mounting position	optional
Product weight	65 g
Electrical connection	8-pin Angled socket Solderable
Operational voltage range DC	≤60 V
Permissible current load	5 A
Cable fitting	Pg 9
Permissible cable diameter	6 mm ... 8 mm
Connection cross section	0.75 mm ²
Degree of protection	IP67
Ambient temperature	-30 °C ... 95 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA
Housing colour	Black
Material union nut	PA
Material electrical contact	Copper Tin-plated