

Clevis foot CRLNG-40

Part number: 161841

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Size | 40 |
| Based on standard | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Mounting position | optional |
| Corrosion resistance class CRC | 4 - Very high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Ambient temperature | -40 °C ... 80 °C |
| Max. load capacity | 1.5 kN |
| Product weight | 161 g |
| Note on materials | RoHS-compliant |
| Material mounting | Electropolished High-alloy steel |
| Material bearing | Polymer |