

Trunnion support CRLNZG-100/125

Part number: 161877

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Size | 100/125 |
| Based on standard | ISO 15552 |
| Corrosion resistance class CRC | 4 - Very high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Ambient temperature | -40 °C ... 150 °C |
| Max. load capacity | 9 kN |
| Product weight | 739 g |
| Note on materials | RoHS-compliant |
| Material mounting | High-alloy stainless steel |
| Material bearing | Polymer |