

# Sub-base PAML-CP-186-HP3-G114

Part number: 1629296

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	186
Nominal size DN	54
Series	L
Operating pressure	0 MPa ... 5 MPa
Operating pressure	0 bar ... 50 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-::-]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C ... 60 °C
Suitable for use with food	See supplementary material information
Media temperature	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Product weight	4600 g
Pneumatic connection, port 1	G1 1/4
Pneumatic connection, port 2	G1 1/4
Note on materials	RoHS-compliant
Material sub-base	Wrought aluminium alloy
Material seals	NBR
Material screws	Stainless steel