

# Sensor bracket DASI-Q11-32-A-SR

Part number: 1631997

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	32
Design	For T-slot
For piston diameter	Diameter 32
Design	Sensor rail
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	42 g
Type of mounting	Clamped in T-slot Via through-hole and screw Via slot nuts
Note on materials	RoHS-compliant
Material screws	Steel Galvanised