

Fibre-optic cable SOEZ-LLG-SE-0,5-M4

Part number: 165357

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Measurement method	Through-beam sensor Light guide
Ambient temperature	-20 °C ... 160 °C
Size	M4
Product weight	46 g
Material housing	Chrome-plated
Setting range upper limit	280 mm
Ambient temperature with moving installation	-20 °C ... 120 °C
Degree of protection	IP54
LABS (PWIS) conformity	VDMA24364-B2-L