

# Pressure regulator LR-3/4-D-O-MAXI-NPT

Part number: 173669

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	Maxi
Series	D
Mounting position	optional
Controller function	Output pressure constant
Symbol	00991559
Operating pressure	1.6 MPa
Operating pressure	16 bar
Pressure regulation range	0.5 bar ... 12 bar
Max. pressure hysteresis	0.04 MPa
Max. pressure hysteresis	0.4 bar
Max. pressure hysteresis	5.8 psi
Standard nominal flow rate (standardised to DIN 1343)	11000 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	700 g
Type of mounting	In-line installation
Pneumatic connection, port 1	3/4 NPT
Pneumatic connection, port 2	3/4 NPT
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	Die-cast zinc