

# Micro filter LFMA-1/8-D-MINI-NPT

Part number: 173724

FESTO



 General operating condition

## Data sheet

Feature	Value
Series	D
Size	Mini
Grade of filtration	0.01 µm
Condensate drain	Manual, non-detenting
Symbol	00991519
Operating pressure	1 bar ... 16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:8:4] Inert gases
Air purity class at output	Compressed air to ISO 8573-1:2010 [1:7:2] Inert gases
Max. standard flow rate for clean air class	360 l/min
Min. standard flow rate for clean air class	80 l/min
Filter efficiency	99.9999 %
Bowl guard	Metal bowl guard
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	1.5 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Residual oil content	0.01 mg/m <sup>3</sup>
Type of mounting	Via mounting bracket
Mounting position	Vertical
Pneumatic connection, port 1	1/8 NPT
Pneumatic connection, port 2	1/8 NPT
Material housing	Die-cast zinc
Material filter	Borosilicate fibre
Material bowl	PC
Note on materials	RoHS-compliant