

Filter combination LFMBA-1/8-D-MINI-NPT

Part number: 173740

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	Mini
Series	D
Mounting position	Vertical
Grade of filtration	0.01 µm
Filter efficiency	99.9999 %
Condensate drain	Manual, non-detenting
Bowl guard	Metal bowl guard
Symbol	00991740
Operating pressure	1 bar ... 16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:8:4] Inert gas
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air to ISO 8573-1:2010 [1:7:2] Inert gases
Media temperature	1.5 °C ... 60 °C
Residual oil content	0.01 mg/m ³
Ambient temperature	-10 °C ... 60 °C
Type of mounting	With accessories
Pneumatic connection, port 1	1/8 NPT
Pneumatic connection, port 2	1/8 NPT
Note on materials	RoHS-compliant
Material filter	Borosilicate fibre
Material housing	Die-cast zinc
Material bowl	PC