

# Lubricator LOE-3/8-D-MIDI-NPT

Part number: 173823

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

Feature	Value
Max. oil capacity	110 cm <sup>3</sup>
Bowl guard	Metal bowl guard
Symbol	00991532
Operating pressure	1.6 MPa
Operating pressure	16 bar
Operating pressure	232 psi
Min. flow rate for lubricator function	8 l/min
Standard nominal flow rate (standardised to DIN 1343)	5500 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gas
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:4:-] Inert gases
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Type of mounting	With accessories
Pneumatic connection, port 1	3/8 NPT
Pneumatic connection, port 2	3/8 NPT
Note on materials	RoHS-compliant
Material bowl	PC