

Trunnion flange ZNCF-40

Part number: 174412

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	40
Based on standard	ISO 15552
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	1.5 kN
Product weight	285 g
Note on materials	RoHS-compliant
Material mounting	Stainless steel casting
Material screws	Steel Galvanised