

Low consumption air gun LSP-1/4-C

Part number: 184318

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Exhaust-air function	Metered blowing
Instructions on use	G1/4 mount screw-in part without flat sealing ring
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Operating pressure	0 psi ... 145 psi
Standard nominal flow rate (standardised to DIN 1343)	120 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
LABS (PWIS) conformity	VDMA24364 zone III
Sound pressure level	90 dB(A)
Ambient temperature	-10 °C ... 50 °C
Product weight	125 g
Pneumatic connection	Female thread G1/4
Material housing	PA6 reinforced