

Plug socket MSSD-ZBZC

Part number: 185521

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Maritime classification	See certificate
Type of mounting	On solenoid valve via self-tapping screw
Mounting position	optional
Product weight	11 g
Electrical connection	Socket
Operational voltage range DC	3 V ... 36 V
Nominal operating voltage DC	24 V
Permissible current load	1 A
Nominal cross section conductor	0.22 mm ² ... 0.34 mm ²
Degree of protection	IP50
Ambient temperature	-10 °C ... 50 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Pollution degree	2
Corrosion resistance class CRC	1 - Low corrosion stress
Material housing	PA