

# Manifold block CPE18-PRSG-3

Part number: 187825

FESTO



 [General operating condition](#)

## Data sheet

| Feature                            | Value  |
|------------------------------------|--|
| Max. number of valve positions     | 3  |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC     | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L  |
| Product weight                     | 225 g  |
| Mounting method for sub-base       | With through-hole<br>With H-rail   |
| Pneumatic connection, port 1       | G1/2   |
| Note on materials                  | RoHS-compliant   |
| Material housing                   | PA-reinforced  |