

# Plastic tubing PUN-CM-4-SW

Part number: 188882

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                  | Value                                     |
|--|---|
| Outside diameter                         | 4 mm                                      |
| Flow-relevant bending radius             | 17 mm                                     |
| Inside diameter                          | 2.5 mm                                    |
| Min. bending radius                      | 8 mm                                      |
| Tubing characteristics                   | Suitable for energy chains                |
| Temperature-dependent operating pressure | -0.095 MPa ... 1 MPa                      |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar                      |
| Temperature-dependent operating pressure | -13.775 psi ... 145 psi                   |
| Surface resistance                       | 0.01 MOhm ... 10 MOhm                     |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:-:-] |
| LABS (PWIS) conformity                   | VDMA24364-B2-L                            |
| Ambient temperature                      | -35 °C ... 60 °C                          |
| Product weight according to length       | 0.00993 kg/m                              |
| Pneumatic connection                     | For push-in connector O.D. 4 mm           |
| Colour                                   | Black                                     |
| Shore hardness                           | D 52 +/-3                                 |
| Note on materials                        | RoHS-compliant                            |
| Material tubing                          | TPE-U(PU)                                 |