

# Suction cup complete holder ESH-HC-3-QS

Part number: 189217

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Height compensator for suction-cup holder	6 mm
Nominal size	3.4 mm
Volume	1.041 cm <sup>3</sup>
Mounting position	Vertical
Design	Vacuum port on top With height compensator
Correlation to suction-cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C ... 60 °C
Product weight	34 g
Type of mounting	Via lock nut
Suction cup mounting	M4
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Material seals	NBR Steel
Material retaining bracket	Tempered steel High-alloy steel