

Suction cup complete holder ESH-HDL-2-QS

Part number: 189245

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Height compensator for suction-cup holder	10 mm
Nominal size	2.2 mm
Volume	0.26 cm ³
Mounting position	Vertical
Design	Vacuum port on side With height compensator
Correlation to suction-cup holder	Size 2
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C ... 60 °C
Product weight	33 g
Type of mounting	Via lock nut
Suction cup mounting	Diameter 4 mm
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Material seals	NBR Steel
Material retaining bracket	Tempered steel High-alloy steel