

Holder for suction cup with connection ESH-HE-5-G1/4

Part number: 189257

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	7 mm
Volume	1.227 cm ³
Mounting position	Any
Design	Vacuum port on top
Correlation to suction-cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	24 g
Type of mounting	With male thread Via vacuum port
Suction cup mounting	M10
Vacuum connection	G1/4
Note on materials	RoHS compliant
Material seals	Wrought aluminium alloy NBR POM Steel
Material retaining bracket	Tempered steel