

Suction cup with connection ESS-80-SN

Part number: 189318

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Min. workpiece radius	400 mm
Nominal size	6 mm
Suction cup diameter	80 mm
Suction cup volume	19.312 cm ³
Position of connection	Top
Mounting position	optional
Symbol	00991485
Correlation to suction-cup holder	Size 5
Suction cup shape	Round, flat
Operating pressure	-0.095 MPa ... 0 MPa
Operating pressure	-0.95 bar ... 0 bar
Operating pressure	-13.775 psi ... 0 psi
Nominal operating pressure	-0.07 MPa
Nominal operating pressure	-0.7 bar
Nominal operating pressure	-10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Suitable for use with food	See supplementary material information
Ambient temperature	-10 °C ... 70 °C
Holding force at nominal operating pressure	309.7 N
Lateral force at nominal operating pressure	315 N
Product weight	133 g
Type of mounting	Via vacuum port
Vacuum connection	M10
Colour	Black
Shore hardness	60 +/- 5
Material screwed plug	POM Nickel-plated steel Steel, galvanised and chrome-plated
Note on materials	RoHS-compliant

Feature	Value
Material suction cup	NBR