

Suction cup without connector ESV-20-SNA

Part number: 190983

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Suction cup diameter	20 mm
Suction cup volume	0.318 cm ³
Position of connection	Top
Mounting position	optional
Special characteristics	Antistatic
Symbol	00991485
Suction cup shape	Round, flat
Operating pressure	-0.095 MPa ... 0 MPa
Operating pressure	-0.95 bar ... 0 bar
Operating pressure	-13.775 psi ... 0 psi
Nominal operating pressure	-0.07 MPa
Nominal operating pressure	-0.7 bar
Nominal operating pressure	-10.15 psi
Surface resistance	≤2.0E-4 MOhm
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-A1-L
Suitable for use with food	See supplementary material information
Ambient temperature	-10 °C ... 70 °C
Holding force at nominal operating pressure	16.3 N
Product weight	1.6 g
Colour	Black/white dot
Shore hardness	50 +/- 5
Note on materials	RoHS-compliant
Material suction cup	NBR