

# Suction cup without connector ESV-80-SU

Part number: 191004

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature                                     | Value  |
|---|--|
| Min. workpiece radius                       | 400 mm   |
| Suction cup diameter                        | 80 mm  |
| Suction cup volume                          | 19.312 cm <sup>3</sup>                           |
| Position of connection                      | Top  |
| Mounting position                           | optional   |
| Symbol                                      | 00991485   |
| Suction cup shape                           | Round, flat                                      |
| Operating pressure                          | -0.095 MPa ... 0 MPa                             |
| Operating pressure                          | -0.95 bar ... 0 bar                              |
| Operating pressure                          | -13.775 psi ... 0 psi                            |
| Nominal operating pressure                  | -0.07 MPa  |
| Nominal operating pressure                  | -0.7 bar   |
| Nominal operating pressure                  | -10.15 psi                                       |
| Operating medium                            | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| LABS (PWIS) conformity                      | VDMA24364 zone III                               |
| Suitable for use with food                  | See supplementary material information           |
| Ambient temperature                         | -20 °C ... 60 °C                                 |
| Holding force at nominal operating pressure | 309.7 N  |
| Product weight                              | 33 g   |
| Colour                                      | Blue   |
| Shore hardness                              | 60 +/- 5   |
| Note on materials                           | RoHS-compliant                                   |
| Material suction cup                        | PUR  |