

Angle compensator ESWA-3

Part number: 191205

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Angle compensation +/-	15 deg
Mounting position	optional
Design	Ball joint
Correlation to suction-cup holder	Size 3
Operating pressure	-0.95 bar ... 4 bar
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C ... 60 °C
Product weight	9 g
Type of mounting	Via male thread
Suction cup mounting	M4
Pneumatic connection	M4
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	Aluminium Brass, nickel-plated