


Mounting plate VN-T3-BP-NRH

Part number: 193641

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	0.5 Nm
Product weight	3.5 g
Type of mounting	With through-hole With H-rail
Material plate	POM-reinforced
Material gate valve	POM