

# Plug socket with cable KMYZ-4-24-0,5-B

Part number: 193690

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                      | Value  |
|--|--|
| Type of mounting                             | On solenoid valve via M2 central screw       |
| Mounting position                            | Any  |
| Product weight                               | 10 g   |
| Electrical connection                        | Angled socket<br>Cable<br>Square design MSZC |
| Operational voltage range DC                 | 3 V ... 36 V                                 |
| Nominal operating voltage DC                 | 24 V   |
| Current rating at 40° C                      | 1 A  |
| Protective conductor connection              | Not provided                                 |
| Cable length                                 | 0.5 m  |
| Cable characteristic                         | Standard                                     |
| Cable structure                              | 2 x 0.35 mm <sup>2</sup>                     |
| Degree of protection                         | IP40   |
| Ambient temperature                          | -10 °C ... 50 °C                             |
| CE mark (see declaration of conformity)      | In accordance with EU RoHS Directive         |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions                      |
| LABS (PWIS) conformity                       | VDMA24364-B2-L                               |
| Note on materials                            | RoHS compliant                               |
| Corrosion resistance class CRC               | 1 - Low corrosion stress                     |
| Material cable sheath                        | PVC  |
| Material housing                             | Process automation                           |
| Material electrical contact                  | Bronze                                       |