

Bellows cylinder EB-385-115

Part number: 193789

FESTO



 General operating condition

Data sheet

Feature	Value
Size	385
Required installation diameter	400 mm
Stroke	115 mm
Max. extended height	175 mm
Max. angle of inclination	15 deg
Max. offset	10 mm
Min. installation height	51 mm
Mounting position	optional
Mode of operation	Single-acting
Symbol	00991205
Operating pressure	0 MPa ... 0.8 MPa
Operating pressure	0 bar ... 8 bar
Operating pressure	0 psi ... 116 psi
Operating medium	Compressed air to ISO 8573-1:2010 [-:::4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 70 °C
Reset force	300 N
Product weight	5900 g
Type of mounting	Via female thread
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material bellows	NR/BR
Material housing	Steel Galvanised